

Testing for the Articles 04012024

ISO 15143-4 (AEMP 2.0) API Access Guide

ISO 15143-3 (AEMP 2.0) API

Assumptions

- API consumer has entered into a valid Digital Marketplace Agreement.
- API consumer has received client credentials (Client ID and Client Secret).
- API consumer has valid Corporate Web Security (CWS ID -Username and Password).
- API consumer is subscribed to the API and will use the API only in accordance with the Digital Marketplace Agreement and Licenses to APIs.

Communications

Sr. No	Sender	Subject	Purpose
1	DigitalMarketplaceTeam@cat.com	** SAVE this Email ** - These Credentials are key to accessing your recent Client credentials and secret request for ISO 15143-3 (AEMP 2.0) API	Email contains client credentials to access ISO 15143-3 (AEMP 2.0) API (to access the API via Postman or other integration)
2	donotreply@cat.com	Your subscription to the ISO 15143-3 (AEMP 2.0) API product has been activated.	Email confirms subscription of ISO 15143-3 (AEMP 2.0) API

Access ISO 15143-3 (AEMP 2.0) API - Postman


Pre-requisites:

What is needed	How to get it
API Client Credentials (Client ID and Client Secret)	From Caterpillar
Postman tool installed in your desktop / PC	https://www.postman.com/downloads/


What is needed	How to get it
Postman collection for ISO 15143-3 (AEMP 2.0) [Postman collection is a set of JSON files]	From Caterpillar

Import ISO API Postman Collection


Step 1: You can click on “Skip and go to the app” to import the Postman collections.*



Step 2: Click on the Import button.




Step 3: Following popup window will open: Click on “Choose Files” button.




Step 4: Select postman collection obtained from Caterpillar Adoption Team (with the meeting invitation).

Step 5: On successful import you can see ISO 15143-3 (AEMP 2.0) API request as follows:




Get OAuth 2.0 Access Token

Step 1: Select Fleet snapshot from the ISO 15143-3 (AEMP 2.0) API from collection and go to the “Authorization” tab and select OAuth 2.0.




Step 2: Select “Request Headers” from drop down as shown in the screen below:

Note: This will add the Authorization field in the header.





Step 3: Select the “Configure new token” option.




Step 4: Enter the below details under “Configure new token” and click on “Get New Access Token” button as shown below:


Field	Value
Token Name	Enter a name for the token (this is just for your reference)
Grant Type	Choose “Client Credentials”
Access Token URL	https://fedlogin.cat.com/as/token.oauth2
Client Id	Enter Client Id (Please get in touch with credential owner)
Client Secret	Enter Client Secret (Please get in touch with credential owner)
Client Authentication	Select “Send as Basic Auth Header” from dropdown



Step 5: The following window will display the new access token:



Step 6: Click "USE TOKEN".



Note: This will add the Authorization field in the header

Fleet Snapshot API

Step1: To obtain the Fleet Snapshot Data in XML Format.

Endpoint URL:

<https://services.cat.com/telematics/iso15143/fleet/{pageNumber}>

Example:

The URL for Fleet Snapshot data in XML format would be:

<https://services.cat.com/telematics/iso15143/fleet/1>


Header:

Accept: application/iso15143-snapshot+xml

Parameter:

1 {PageNumber}

Screens from Postman:



Step 2: Repeat the Authorization step from section 3.2.

Step 3: Click SEND. Screen shot of the response:


```
Body Cookies Headers (17) Test Results Status: 200 OK Time: 2.00 s Size: 95.68 KB Save as Example
Pretty Raw Preview Visualize XML
4 <rel>Current</rel>
5 <href>https://api.cat.com/telematics/iso15143/fleet/1</href>
6 </Links>
7 <Links>
8 <rel>Next</rel>
9 <href>https://api.cat.com/telematics/iso15143/fleet/2</href>
10 </Links>
11 <Links>
12 <rel>Last</rel>
13 <href>https://api.cat.com/telematics/iso15143/fleet/127</href>
14 </Links>
15 <Links>
16 <rel>First</rel>
17 <href>https://api.cat.com/telematics/iso15143/fleet/1</href>
18 </Links>
19 <Equipment>
20 <EquipmentHeader>
21 <OEMName>CAT</OEMName>
22 <Model>23203LRC</Model>
23 <SerialNumber>PWN00115</SerialNumber>
24 </EquipmentHeader>
25 <Location datetime="2023-05-23T07:12:11Z">
26 <Latitude>43.087470</Latitude>
27 <Longitude>79.899800</Longitude>
28 <Altitude>68.000000</Altitude>
29 <AltitudeUnits>metre</AltitudeUnits>
30 </Location>
31 <CumulativeIdleHours datetime="2023-05-22T19:02:53Z">
32 <Hours>272.1</Hours>
33 </CumulativeIdleHours>
34 <CumulativeOperatingHours datetime="2023-05-23T07:12:11Z">
35 <Hours>4748.6</Hours>
36 </CumulativeOperatingHours>
```

Step 4: Fleet Snapshot Data in JSON Format.

NOTE: Follow the same steps from this Section, but change "Accept Type" in header to "application/iso15143-snapshot+json".

Equipment Snapshot API

Step 1: To obtain the Equipment Snapshot Data in JSON Format:

Endpoint URL:

<https://services.cat.com/telematics/iso15143/fleet/equipment/makeModelSerial/{make}/{model}/{serialNumber}>

Example: To get the Equipment Snapshot data for the following asset in JSON format.

Make: CAT

Model: MH3026

Serial Number: FB999999

Equipment Snapshot URL:

<https://services.cat.com/telematics/iso15143/fleet/equipment/makeModelSerial/CAT/MH3026/FB999999>

Header:

Accept: application/iso15143-snapshot+json

Screens from Postman:

ISO15143 API (AEMP 2.0) Collection_1.1 - Production Copy 2 / Equipment Snapshot (individual) - JSON

GET <https://services.cat.com/telematics/iso15143/fleet/equipment/makeModelSerial/CAT/232D3LRC/PWN00115/> Send

Params Authorization Headers (8) Body Pre-request Script Tests Settings Cookies

Query Params

Key	Value	Description
Key	Value	Description

ISO15143 API (AEMP 2.0) Collection_1.1 - Production Copy 2 / Equipment Snapshot (individual) - JSON

GET <https://services.cat.com/telematics/iso15143/fleet/equipment/makeModelSerial/CAT/232D3LRC/PWN00115/> Send

Params Authorization Headers (8) Body Pre-request Script Tests Settings Cookies

Headers 7 hidden

Key	Value	Description
<input checked="" type="checkbox"/> accept	application/iso15143-snapshot+json	
Key	Value	Description

Step 2: Repeat the Authorization step from section 3.2.

Step 3: Click SEND. See the response:

Body Cookies Headers (17) Test Results Status: 200 OK Time: 1103 ms Size: 2.13 KB Save as Example

Pretty Raw Preview Visualize JSON

```

1  {
2    "Links": [
3      {
4        "Rel": "Current",
5        "Href": "https://api.cat.com/telematics/iso15143/fleet/equipment/makeModelSerial/CAT/232D3LRC/PWN00115"
6      }
7    ],
8    "Equipment": [
9      {
10     "EquipmentHeader": {
11       "OEMName": "CAT",
12       "Model": "232D3LRC",
13       "EquipmentID": "232D3 NSI 8",
14       "SerialNumber": "PWN00115"
15     },
16     "Location": {
17       "Latitude": 13.087470,
18       "Longitude": 79.899800,
19       "Altitude": 58.000000,
20       "AltitudeUnits": "metre",
21       "Datetime": "2023-05-23T07:12:11Z"
22     },
23     "CumulativeIdleHours": {
24       "Hours": 272.1,
25       "Datetime": "2023-05-22T19:02:53Z"
26     },
27     "CumulativeOperatingHours": {
28       "Hours": 4748.5,
29       "Datetime": "2023-05-23T07:12:11Z"

```

Step 4: Equipment Snapshot Data in XML Format:

Follow the same steps from this Section, but change "Accept Type" in header to "application/iso15143-snapshot+xml".

Timeseries Fault Code API

Step 1: To obtain the Timeseries Fault Code Data in JSON Format:

Endpoint URL:

<https://services.cat.com/telematics/iso15143/fleet/equipment/makeModelSerial/{make}/{model}/{serialNumber}/faults/{startDateUTC}/{endDateUTC}/{pageNumber}>

Example: To get the Timeseries Fault Code data for the following asset in XML format:

Make: CAT

Model: MH3026

Serial Number: FB999999

startDateUTC : 2019-05-07T00:00:00Z

endDateUTC: 2019-05-17T00:00:00Z

pageNumber = 1

Timeseries Fault code URL:

<https://services.cat.com/telematics/iso15143/fleet/equipment/makeModelSerial/CAT/MH3026/FB999999/faults/2019-05-07T00:00:00Z/2019-05-17T00:00:00Z/1>

Header:

Accept: application/iso15143-faults+ json

Screens from Postman:


The top screenshot shows a GET request in Postman with the following URL: `https://services.cat.com/telematics/iso15143/equipment/makeModelSerial/CAT/3406E/SIT13632/faults/2023-04-10T10:38:41Z/2023-05-23T07:11:08Z/1`. The Authorization tab is selected, showing a Bearer Token with the value `eyJhbGciOiJIUzI1NiIsImtpZCI6IjEILCJwa55F...`. A warning message states: "Heads up! These parameters hold sensitive data. To keep this data secure while working in a collaborative environment, we recommend using variables. Learn more about variables".

The bottom screenshot shows the same request with the Headers tab selected. The 'Accept' header is set to `application/iso15143-faults+json`. The Headers table is as follows:

Key	Value	Description
<input checked="" type="checkbox"/> Accept	application/iso15143-faults+json	
Key	Value	Description

Step 2: Repeat the Authorization step from section 3.2.

Step 3: Click SEND. See example below:



The screenshot shows a web browser's developer console with the 'Body' tab selected. The response is a JSON array of fault codes. The first fault code has a severity of 'Medium' and a description related to 'Abnormal Frequency, Pulse Width, or Period'. The second fault code has a severity of 'High' and a description related to 'Current Below Normal'. The console also shows the status '200 OK', response time '796 ms', and size '3.18 KB'.

```
15 ],
16   "FaultCode": [
17     {
18       "CodeIdentifier": "5246-8",
19       "CodeDescription": "Aftertreatment SCR Operator Inducement Severity: Abnormal Frequency,
20         Pulse Width, or Period",
21       "CodeSeverity": "Medium",
22       "CodeSource": "Machine Control",
23       "Datetime": "2023-05-12T20:03:42Z"
24     },
25     {
26       "CodeIdentifier": "5246-5",
27       "CodeDescription": "Aftertreatment SCR Operator Inducement Severity: Current Below Normal",
28       "CodeSeverity": "High",
29       "CodeSource": "Machine Control",
```

Step 4: Timeseries Fault Code Data in XML Format:

Follow the same steps in this Section, but change "Accept Type" in header to "application/iso15143-faults+xml".

Timeseries Location API

Step 1: To obtain the Timeseries Location in XML Format:

Endpoint URL:

<https://services.cat.com/catDigital/iso15143/v1/fleet/equipment/makeModelSerial/{make}/{model}/{serialNumber}/locations/{startDateUTC}/{endDateUTC}/{pageNumber}>

Example: To get the Asset location data for the following asset in XML format:

Make: CAT

Model: 930K

Serial Number: DYB64103

startDateUTC : 22-12-12T00:00:00Z

endDateUTC: 2022-12-21T00:00:00Z

pageNumber = 1

Timeseries Locations URL:

<https://services.cat.com/catDigital/iso15143/v1/fleet/equipment/makeModelSerial/CAT/930K/DYB64103/locations/2022-12-12T00:00:00Z/2022-12-21T00:00:00Z/1>

Header:

Accept: application/xml

Screens from Postman:

The first screenshot shows a GET request in Postman with the URL: `https://api.cat.com/catDigital/iso15143/v1/fleet/equipment/makeModelSerial/CAT/930K/DYB64103/locations/2022-12-12T00:00:00Z/2022-12-21T00:00:00Z/1`. The Params tab is active, showing a table with columns KEY, VALUE, and DESCRIPTION. The second screenshot shows the same request with the Headers tab active. It displays 7 hidden headers, including `x-cat-dev: true` and `accept: application/xml`. The status bar at the bottom indicates a 200 OK response with a time of 2.23 s and a size of 24.54 KB.

Step 2: Repeat the Authorization step from section 3.2.

Step 3: Click SEND. See example below:

The screenshot shows the response body in XML format. The XML structure includes a `<Links>` section with a `<rel>First</rel>` and a `<href>` pointing to the API endpoint. It also contains two `<Location>` elements, each with attributes for `datetime`, `Latitude`, `Longitude`, `Altitude`, `AltitudeUnits`, `ChinaCoordinateId`, and `Address`.

Step 4: Timeseries Location Data in JSON Format:

Follow the same steps in this Section, but change "Accept Type" in header to "application/json."

Timeseries Switch Status API

Step 1: To obtain the Timeseries Switch status Data in XML Format:

Endpoint URL:

<https://services.cat.com/catDigital/iso15143/v1/fleet/equipment/makeModelSerial/{make}/{model}/{serialNumber}/switchStatus/{startDateUTC}/{endDateUTC}/{pageNumber}>

Example: To get the Timeseries switch status data for the following asset in XML format:

Make: CAT

Model: C9.3

Serial Number: RFS45659

startDateUTC : 2022-12-12T00:00:00Z

endDateUTC: 2022-12-21T00:00:00Z

pageNumber = 1


Timeseries switch status URL:

<https://services.cat.com/catDigital/iso15143/v1/fleet/equipment/makeModelSerial/CAT/C9.3/RFS45659/switchStatus/2022-12-12T00:00:00Z/2022-12-21T00:00:00Z/1>

Header:


Accept: application/xml

Screens from Postman:



The screenshot shows the Postman interface for a GET request. The URL is <https://api.cat.com/catDigital/iso15143/v1/fleet/equipment/makeModelSerial/CAT/930K/DYB64103/switchStatus/2022-12-06T05:41:08Z/2022-12-07T05:28:12Z/1>. The request is configured with a GET method and a 'Send' button. The interface includes tabs for Params, Authorization, Headers (9), Body, Pre-request Script, Tests, and Settings. A 'Query Params' table is visible below the URL field.

KEY	VALUE	DESCRIPTION	...	Bulk Edit
Key	Value	Description		




Step2: Repeat the Authorization step from section 3.2.

Step3: Click SEND. See example.

Important! The API is currently available only to a limited group of pilot users. The API availability to dealers at large will be announced after the pilot completion.

The Dealer ERP Customer Master API allows dealers to integrate their ERP systems with Caterpillar Customer Master by sending their customer data to Caterpillar in near real time. The API provides the same capabilities to create customers and associate them with dealerships as the [Customer Admin Tool](#) web application (<https://mycustomer.cat.com>).



Security

The API uses the OAuth 2.0 protocol for authorization. In order to access the API, an OAuth access token is required in the request headers of each API call. A valid OAuth client ID and client secret is required to obtain an OAuth access token.

The following basic information is required to authenticate and generate the token.

Field	Value
Grant Type	Set this to <code>client_credentials</code> .
Token URL	Production: https://fedlogin.cat.com/as/token.oauth2 QA: https://fedloginqa.cat.com/as/token.oauth2
Client ID	Your application's Client ID. Contact your credentials owner.
Client Secret	Your application's Client Secret. Contact your credentials owner.

An OAuth token expires after 60 minutes. An expired token will need to be replaced with a new token.

Additional OAuth information can be found in the [Caterpillar OAuth 2.0 Documentation](#).

API Environments

The API is available in QA and production environments:

- QA: <https://services-int.cat.com/catDigital/customerMaster/dealerErp/v1>
- Production: <https://services.cat.com/catDigital/customerMaster/dealerErp/v1>

API Reference Information

Detailed reference information about the API input parameters, request bodies, responses, and error messages can be found in the Dealer ERP Customer Master API [reference documentation](#)

Workflow

Caterpillar Customer Master is the Caterpillar database of customers associated with dealers.

A customer organization represents a customer that can be associated with multiple dealers.

A *dealer customer* is an instance of a customer organization associated with a specific dealer (dealer code). A dealer customer is identified by the combination of a dealer code and DCN (dealer customer number) joined with a pipe (|), for example, "TD68|245TRSSDG343456.

Use the Dealer ERP Customer Master API to associate a new or existing customer organization with a dealer (single dealer code). The workflow is as follows:

- When the API user submits the request, a search is performed to find the customer organization in the customer master database.

- API uses following search criteria to find the org (all must match):

- Customer organization name is similar to input string
- Country code matches to the input value
- Address1 field is similar to input string
- Postal code is similar to input value OR city name and state match input values
- If the customer organization is not found in the database, the customer organization is created using `businessName`, `alternateName`, address, email, and phones with the status of `ACTIVE`.
- If a customer organization is found, it will be associated with the specified dealer code.
- When a customer organization is associated the specified dealer code, the resulting DCN (`dealerCode` and `dealerCustomerNumber` combination) is validated against in the customer master database.

- If the DCN exists and is not associated to any customer organization, then an association is created with the provided `customerOrganizationIdentifier` and the DCN and a 200 response is returned.
- If the DCN exists in the customer master database and is associated to any customer organization, a 400 response code is returned.
- If the DCN does not exist in the database, then the dealer customer is created using `businessName,alternateName,dealerCustomerNumber, dealerCode, dealerType=REVENUE` (by default), address, email, phones attributes and associated to customer organization.

- To associate the customer organization with additional dealer codes, submit additional requests using the `customerOrganizationIdentifier` returned by the original call. See examples below.

Add a Customer to a Dealer

Use the `POST /dealerCustomers/associate` endpoint to add a customer to a dealer (i.e., create a *dealer customer* by associating a *customer organization* with a dealer code):

```
curl --location --request POST
'https://api-int.cat.com/catDigital/customerMaster/dealerErp/v1/dealerCustomers/
associate#39; \ --header 'Authorization: Bearer {Bearer Token}' \ --header
'Content-Type: application/json' \ --data-raw '{ "businessName": "DIY Digging,
Inc", "alternateName": "NW53655HGFD ALT", "dealerCustomerNumber":
"245TRSSDG343456", "dealerCode": "TD68", "addresses": [ {
"addressType": "MAIN OFFICE", "address1": "123 Park Lane", "address2":
"", "address3": "", "countryCode": "USA", "stateOrProvinceCode":
"IL", "subdivisionCode": "", "cityName": "Peoria", "postalCode":
"61607" } ], "emails": [ { "emailAddress": "TRHW465@CAT.COM",
"emailType": "PRIMARY" } ], "phones": [ { "phoneNumber": "+1
312-345-7535", "phoneType": "PRIMARY" } ]}'
```

To associate the customer organization with additional dealer codes, submit additional requests including the `customerOrganizationIdentifier` value from the response to the first request:

```
curl --location --request POST
'https://services.cat.com/customerMaster/dealerErp/v1/dealerCustomers/associate&
#39; --header 'Authorization: {Bearer Token}''{
"customerOrganizationIdentifier": "2974527631", "businessName": "DIY Digging,
```

```
Inc", "alternateName": "Ajay Construction", "dealerCustomerNumber":
"245TRSSDG343456", "dealerCode": "TD69", "addresses": [  {
"addressType": "MAIN OFFICE",      "address1": "123 Park Lane",      "address2":
"",      "address3": "",      "countryCode": "USA",      "stateOrProvinceCode":
"IL",      "subdivisionCode": "",      "cityName": "Peoria",      "postalCode":
"61607"  }  ], "emails": [  {      "emailAddress": "TRHW465@CAT.COM",
"emailType": "PRIMARY"  }  ], "phones": [  {      "phoneNumber": "+1
312-345-7535",      "phoneType": "PRIMARY"  }  ]}'
```

Request body

The following is a complete list of the required and optional request attributes.

Required

- **businessName**: The customer organization or dealer customer business name represents the business name of the customer organization or dealer customer.
- **dealerCustomerNumber**: The unique identifier of the customer in the dealer ERP system. Dealer customer number is part of the DCN (**dealerCode** and **dealerCustomerNumber** combination) identifier.

- **dealerCode**: The Caterpillar-assigned dealer code derived from dealer ERP source system.
- **addresses**: Customer address. The address object passed in the request to dealer ERP customer master API must have **MAIN OFFICE** address type. The address is NOT validated against a GIS database.

Optional

- **emails**: Details of customer or dealer customer email object to be added for the customer.
- **phones**: Order the results in either ascending or descending order.
- **customerOrganizationIdentifier**: The unique identifier of the customer organization. Specify the value to associate the customer organization with additional dealer codes. You can get the value from a successful response to the initial API call.
- **alternateName**: The alternate business name of the customer organization or dealer customer.

Response

A successful (201) response is as follow:

```
{ "customerOrganization": { "customerOrganizationDetails": {
"businessName": "DIY Digging, Inc", "alternateName": "Ajay Construction",
"customerOrganizationIdentifier": "2974527631", "topLevelIndicator": true,
"parentOrganizationIdentifier": "2974527631", "updateTime":
"2023-04-03T20:05:17.947Z", "owningDealerCode": "TD68",
"hasAssociatedDealerCustomers": true, "managedAccountIndicator": false,
"status": "ACTIVE", "locked": false }, "addresses": [ {
"address1": "123 Park Lane", "address2": null, "address3": null,
"cityName": "Peoria", "stateOrProvinceCode": "IL", "postalCode":
"61607", "countryCode": "USA", "addressType": "PRIMARY" }
], "phones": [ { "phoneNumber": "+1 312-345-7535",
"phoneType": "PRIMARY" } ], "emails": [ { "emailAddress":
"TRHW465@CAT.COM", "emailType": "PRIMARY" } ],
"dealerCustomerAssociations": [ { "dealerCustomerIdentifier":
"TD68|245TRSSDG343456" } ] }, "dealerCustomerOrganization": {
"dealerCustomerDetails": { "dealerCode": "TD68",
"dealerCustomerNumber": "245TRSSDG343456", "dealerCustomerBusinessName":
"DIY Digging, Inc", "dealerCustomerAlternateName": "Ajay Construction",
"dealerCustomerIdentifier": "TD68|245TRSSDG343456", "updateTime":
"2023-04-03 20:05:18.403862757", "type": "REVENUE", "status": "ACTIVE"
}, "dealerCustomerAddresses": [ { "address1": "123 Park Lane",
"address2": null, "address3": null, "cityName": "Peoria",
"stateOrProvinceCode": "IL", "postalCode": "61607", "countryCode":
"USA", "addressType": "MAIN OFFICE" } ],
"dealerCustomerPhones": [ { "phoneNumber": "+1 312-345-7535",
"phoneType": "PRIMARY" } ], "dealerCustomerEmails": [ {
"emailAddress": "TRHW465@CAT.COM", "emailType": "PRIMARY" } ] }}
```

An error response provides detailed information about the cause of the error:

```
{ "code": "400", "description": "Dealer Customer already has an associated
customer organization."}
```

Testing Procedures

Note: Before testing the API, it is strongly recommended that you set up access to the [Customer Admin Tool](#) web application, if you don't already have it. You will be prompted to request access when you navigate to the application URL.

- Use the QA environment for testing.
- Test the API by passing a valid request. Use a valid dealer code and other request body attributes per the OpenAPI specification.
- To verify the result, check the response body and confirm that the customer is created successfully using the [Customer Admin Tool](#) web application.
- You can also use the [Customer Admin Tool](#) web application to delete the test data you create in the QA environment.

Additional Documentation

The following additional documentation is available as part of the Dealer ERP Customer Master:

- Postman collection:

<https://digital.cat.com/knowledge-hub/document/dealer-erp-customer-master-api-postman-collection>

Change History

Date	Author	Description of Change
04-13-2023	Andrei Essaoulov	Updated the guide for the pilot.
03-10-2023	Mikhail Gavrilov	New document.